

# Datamate Tooling

- ❖ Instruction sheets can be accessed at [www.harwin.com/instructions](http://www.harwin.com/instructions).
- ❖ A Datamate Crimping Instruction video is available at [www.harwin.com/harwintv](http://www.harwin.com/harwintv).

INSERTION/REMOVAL TOOL	REMOVAL TOOL								
<ul style="list-style-type: none"> <li>❖ For inserting crimped contacts into the rear of mouldings.</li> <li>❖ Instruction sheet available.</li> <li>❖ Suitable for all Datamate signal Barrel crimp contacts.</li> </ul>  <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="background-color: #f4a460;">ORDER CODE</th> </tr> </thead> <tbody> <tr> <td>Barrel Signal crimps for L-Tek, J-Tek &amp; Mix-Tek</td> <td style="text-align: center;"><b>Z80-280</b></td> </tr> </tbody> </table>	ORDER CODE		Barrel Signal crimps for L-Tek, J-Tek & Mix-Tek	<b>Z80-280</b>	<ul style="list-style-type: none"> <li>❖ To aid removal of special cable contacts from Mix-Tek connectors.</li> </ul>  <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="background-color: #f4a460;">ORDER CODE</th> </tr> </thead> <tbody> <tr> <td>Mix-Tek special cable connectors</td> <td style="text-align: center;"><b>Z80-290</b></td> </tr> </tbody> </table>	ORDER CODE		Mix-Tek special cable connectors	<b>Z80-290</b>
ORDER CODE									
Barrel Signal crimps for L-Tek, J-Tek & Mix-Tek	<b>Z80-280</b>								
ORDER CODE									
Mix-Tek special cable connectors	<b>Z80-290</b>								
SEPARATOR TOOL	SCREWDRIVER								
<ul style="list-style-type: none"> <li>❖ Recommended for unplugging L-Tek latched connectors (tool releases the latches prior to disengagement).</li> <li>❖ Can also be used with unlatched and friction latched connectors.</li> <li>❖ Suitable for all sizes.</li> </ul>  <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="background-color: #f4a460;">ORDER CODE</th> </tr> </thead> <tbody> <tr> <td>L-Tek</td> <td style="text-align: center;"><b>Z80-299</b></td> </tr> </tbody> </table>	ORDER CODE		L-Tek	<b>Z80-299</b>	<ul style="list-style-type: none"> <li>❖ Recommended for use on J-Tek board mount nuts.</li> <li>❖ Board mount nuts and bolts to be tightened to a torque of 21 ±2cmN.</li> </ul>  <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="background-color: #f4a460;">ORDER CODE</th> </tr> </thead> <tbody> <tr> <td>J-Tek screwdriver</td> <td style="text-align: center;"><b>Z80-298</b></td> </tr> </tbody> </table>	ORDER CODE		J-Tek screwdriver	<b>Z80-298</b>
ORDER CODE									
L-Tek	<b>Z80-299</b>								
ORDER CODE									
J-Tek screwdriver	<b>Z80-298</b>								